



Desiccant in Tyvek<sup>®</sup> Pouch

Desiccant in Kraft Pouch

Tyvek®	Item Number	Pouches per Container	Pouch Size			
Pouch			Width (in)	Length (in)	Width (mm)	Length (mm)
1/6 Unit	1/6PLDES1200	1200	2.125	2.125	54	54
1/3 Unit	1/3PLDES700	700	2.125	2.5	54	64
1/2 Unit	<u>1/2PLDES550</u>	550	2125	2.875	54	73
1 Unit	1PLDES300	300	3.00	4.50	76	114
1 Unit	1PLDES1800	1800	3.00	4.50	76	114
2 Unit	2PLDES150	150	5.00	4.50	127	114
4 Unit	4PLDES500	500	5.00	6.250	127	159
8 Unit	8PLDES300	300	4.50	8.50	114	216
16 Unit	16PLDES150	150	4.50	11.00	114	279

Kraft	Item Number	Pouches per Container	Pouch Size			
Pouch			Width (in)	Length (in)	Width (mm)	Length (mm)
1/2 Unit	<u>1/2KDES550</u>	550	2.375	3.50	60	89

## **RoHS 3, REACH and Conflict Minerals Statement**

None of the RoHS 3 restricted materials, or REACH substances of very high concern as of 2017/07/07, or Toxic in Packaging substances are intentionally added in manufacturing this product. Ref: European Union Directive 2011/65/EU and Regulation (EC) No. 1907/2006/CE. See <u>SCS Warranty, Limitation of Liability and Remedies</u>

Made in North America.

Specifications and procedures subject to change without notice.

## SCS

Description

This efficient desiccant begins working by absorbing airborne moisture left inside the bag when you've finished vacuum packaging, capturing moisture that manages to pass through the bag material. Secured in a strong pouch of either clean room grade, sulphur-free, non-woven Tyvek<sup>®</sup> or economical kraft paper, desiccant helps keep your devices dry, even through unexpected shipping delays or longer than anticipated storage time.

## **Specifications**

Properties Pouch Unit Sizes Media Packaging **Typical Values** Non-Woven Tyvek® or Kraft Paper 1/6, 1/3, 1/2, 1, 2, 4, 8, 16 Montmorillonite Clay Air-tight pails or drums

The recommended amount of desiccant is dependent on the interior surface area of the bag to be used. Below is a reference table indicating recommended minimum amounts of desiccant that should be used with <u>Moisture Barrier Bags</u>. Note: number units rounded up.

As packaged SCS Desiccant in Tyvek<sup>®</sup> and Kraft pouches meets MIL-D-3464, Type I and II and is on the QPL (Qualified Product List).

INTERIOR BAG	NUMBER OF DESICCANT UNITS				
SURFACE AREA*	**MIH <20%	MIH <30%	MIH < 40%		
100 sq. in.	1.5	1.0	1.0		
130 sq. in.	2.0	1.5	1.0		
160 sq. in.	2.0	1.5	1.5		
200 sq. in.	2.5	2.0	1.5		
240 sq. in.	3.0	2.0	1.5		
290 sq. in.	4.0	2.5	2.0		
340 sq. in.	4.5	3.0	2.5		
390 sq. in.	5.0	3.5	2.5		
450 sq. in.	5.5	4.0	3.0		
510 sq. in.	6.5	4.5	3.5		
580 sq. in.	7.5	5.0	4.0		
650 sq. in.	8.0	5.5	4.0		
720 sq. in.	9.0	6.0	4.5		

Table for recommended desiccant usage. Information taken out of EIA-583, Table 1, Page 8. \*To measure interior bag surface area, multiply length x width x 2

\*\*MIH = Maximum Interior Humidity (%)

DESICCANT - TYVEK <sup>®</sup> OR KRAFT PAPER POUCH			
926 JR Industrial Drive, Sanford, NC 27332 WEB SITE: <u>StaticControl.com</u> PHONE (919) 718-0000	DRAWING NUMBER DESICCANT	DATE September 2017	

## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SCS:

1/2KDES550 1/3PLDES700 4PLDES500 8PLDES300 1/6PLDES1200 2PLDES150 1/2PLDES550